

The fitting of the appliance should only be carried out by a authorised person/licensed gasfitter. Please read the safety regulations.
See the data plate for information regarding the total gas consumption, gas type and gas pressure.

Preparations for installation

Pictograms used

Important information

Gas connection

Electrical connection



1/2" ISO 228 / 1/2" ISO 7-1



The gas connection must comply with national and local regulations.

The hotplate can be connected with rigid pipe as specified in AS/NZS 5601.1 current edition.

When the appliance is connected with a hose assembly, the supply point shall be accessible with the appliance installed.


	A (mm)	B (mm)	C (mm)	D (mm)
HG16	600	526	48	520
HG17	750	526	48	594
HG19	900	526	48	514

Accessibility!

Free space around appliance
Rangehoods and exhaust fans shall be installed in accordance with manufacturers instructions.

For an overhead exhaust fan A>750 mm!

A (mm)	B (mm)	C (mm)	D (mm)
HG16	min. 650 min. 600 min. 450 min. 120		
HG17	min. 650 min. 750 min. 450 min. 120		
HG19	min. 650 min. 900 min. 450 min. 120		



240 V - 50 Hz - max. 20 W



This appliance must be earthed

The electrical connection must comply with national and local regulations.

A (<mm)	B (mm)	C (mm)	D (<mm)	E (<mm)	F (>mm)	G	H
HG16	600	560	490	60	50	50	100
HG17	600	560	490	60	50	50	100
HG19	600	860	490	60	50	55	100


Y: metal Gas supply valve shall be accessible

X: safety hose Gas supply valve shall be accessible


x < 60° C

Placing sealing tape

For stainless steel drip tray





Gas connection




Fitting of appliance regulator for Natural gas or test point adaptor for LPG. **Check and set the gas pressure with appliance operating!**

Building in



Connecting and testing



Check that the connections are gastight.
Test the working of the appliance!
Check the ignition of all burners individually and combined.



	Simmer	Normal	Large	Wok
HG16	1	2	-	1
HG17	1	2	1	1
HG19	2	2	2	-

Gas	Burner	Injector burner (mm)	Adj. Screw (mm)	Burner rate (MJ/h)	Gas pressure (kPa)
Natural gas (NG)	Small	0.90	0.45	4.00	1.0
	Medium	1.17	0.60	6.70	
	Large	1.31	0.65	8.60	
	Wok	1.60 + 0.65	0.60	15.70	
ULPG	Small	0.46	0.26	2.80	2.75
	Medium	0.60	0.30	4.90	
	Large	0.72	0.36	7.10	
	Wok	0.93 + 0.40	0.40	14.50	