



Hinweis für Vergleichsprüfung nach AS/NZS 2007

Einordnung nach Normvorgabe
 Einordnungsbeispiel: siehe Bilder A – D
 Fassungsvermögen: 14 IEC
 Maßgedecke
 Vergleichsprogramm: Normal 45 °
 Klarspülereinstellung: 5
 Referenzreiniger: 32,5 g in die
 Reinigerkammer einfüllen.
 Die Tür sollte zur Verbesserung der
 Trocknungsleistung nach Programmende
 um ca. 50mm geöffnet werden.
 Bei höhenverstellbarem Oberkorb muss
 der Oberkorb in die obere Stellung
 eingesetzt werden.
 Bei Abweichungen:
 Wird von der angegebenen
 Vergleichsprüfung, z.B.
 Anschmutzungen, Geschirr- und
 Besteckart usw., abgewichen, ist vor
 Testbeginn mit dem
 Gerätehersteller Kontakt aufzunehmen.

Information about comparability test in accordance with AS/NZS 2007

Appliance loaded in accordance with
 standard specifications,
 Loading example: see Figs. A – D,
 Capacity: 14 IEC place settings.
 Comparability programme: Normal 45 °
 Rinse aid setting: 5
 Reference cleaner: 32,5 g into the
 dispenser
 The door should be opened at the end of
 cycle approximately 50mm for improved
 drying performance.
 If the top basket is height-adjustable, it
 must be inserted in the upper position.
 If there are deviations from the specified
 comparability tests, e.g. soiling, type of
 dishes and cutlery, etc., please contact
 the appliance manufacturer before
 starting the test.